CPAP VT 30D







On Screen Report

Simplest way to get 365 days report in sleep report menu.



Gender Selection

Gender Selection helps to give a Soft/Standard response to the selected gender accordingly.

Technical Specification

Modes Operating/ Monitoring Range	CPAP, Auto CPAP 4-20 CmH2O	
Sound Pressure Level	<28 dBA with uncertainty of 2 dBA	
Leak Compensation	Auto	
Peak Flow	240 LPM	
Ramp Time	Off, Auto, 5-45 mins	
A-Flex (Expiratory Pressure refief)	On/ Off, 1-3 levels	
Gender Selection	Male/ Female	
Humidification Level	Off, 1-5 level (80°C max)	
Display	2.8 in LCD	
Alarms	Leak Alert	
Data Management	1/7/31 days, 6 months, 1 year of detailed data.	
Dimensions (LxWxH)	280x140x95 mm (Device with Humidifier)	
Weight	1700 g (Device with Humidifier)	
Power Adapter	Input Range : 100-240V, 50/60 H², 4A 90 Watt, Over voltage protection Auto Controlled Temp variation	
Battery Backup	External (2-8 Hrs)	
Operating Temperature/ Humidity/ Altitude	+5 °c to +35 °c/10-95% relative humidity, non-condensing/sea level to 2,591 m, air pressure range 735 hpa to 1013 hpa	
Storage and Transport Temperature/Humidity	-20 °c to +60 °c / 5-95% relative humidity, non-condensing	
Supplement Oxygen	Maximum Flow: 4L/min (CPAP)	
Standard Air Filter	Pollen Filter (Washable)	
Tubing	Standard (19 mm)	
Air Outlet	22 mm Air Outlet (STD)	
Warranty	2 Years	
Conforms to Standards	IEC 60601-1-1 IEC 60601-1-2 IEC 80601-2-12 CDSCO	Class 2 (double insulated, Type BF, Ingress Protection IP22)

Key Features

A-Flex

i-Mode

This feature will turn the device **On** for you have the mask on without the need to press any buttons and will also turn the device **Off** once you take your mask Off.

Integrated Humidification

Product Code

VT 30 **D**



















Experience restful nights with our whisper-quiet CPAP device. It delivers all the therapy that ensure you to wake up refreshed and energized each morning, with enhanced monitoring.

RESPIRARE VT 30D



Quietest CPAP

Sleep Better. Breathe Better